







Wet Electrolyte Tantalum Capacitor CA301 series

4, How to order

(Part No. **GTCA301-107M0162B**)

GT	CA301	107	M	016	2	B
----	-------	-----	---	-----	---	---

Notes

- 1 Tantalum capacitors can't been measured by multimeter (Easily cause irreversible damage and lead to reject)
- 2 Capacitance, DF measure frequency: 100Hz $U=2.2_{-1.0}^0V$ $U_{-}=1.0_{-0.5}^0V$ (effective value)
- 3 Measure leakage current above 85 ,please use derated voltage.
- 4 Special size and big capacitance products, please negotiate with us